Industrial Light Commercial Generators

25, 30, 36 kW



RELIABLE BACKUP POWER

THAT LIKES TO KEEP QUIET.

Our new line of standby generators is specifically designed for industrial light commercial applications including small retail, commercial and municipal buildings, universities and apartment complexes.

RUNS QUIETLY AND EFFICIENTLY

Sound-attenuated enclosure and new KOHLER $_{\odot}$ 2.2 L turbocharged engine keep noise to a minimum.

INDUSTRY CERTIFIED

Designed to meet NFPA 110 Level 1 requirements when equipped with required accessories and installed per NFPA 110 standards.

RUST-RESISTANT

KOHLER Power Armor $_{\mbox{\tiny TM}}$ provides corrosion resistance in harsh conditions.

5-YEAR WARRANTY

Comes with a standard 5-year/2,000-hour warranty with optional extended warranty.



1. SOUND ENCLOSURE*

Durable aluminum sound-attenuating enclosure with optional windload

2. ALTERNATOR

Our wound field excitation system with its unique PowerBoost... design delivers great voltage response and short-circuit capability

Brushless, rotating-field alternator has broad-range reconnectability

3. APM402 CONTROLLER

Provides advanced control, system monitoring and system diagnostics for optimum performance and compatibility

4. FUEL SYSTEM

Simple field conversion between natural gas and LPG fuels while maintaining emission certification

5. ENGINE FEATURES

Powerful and reliable 2.2 L turbocharged liquid-cooled engine and electronic engine management system

6. INNOVATIVE COOLING SYSTEM

Electronically controlled fan speeds minimize generator set sound signature

*Sound level - log average @ 7m (23ft) at no load.

| MODEL | | 25CCL, 30CCL, 36CCL |
|---------------------|-------|--|
| POWER NODES | | 25, 30, 36 kW |
| FUEL TYPE | | Natural Gas or Liquid Propane Vapor |
| OPERATING SPEED | | 1800 RPM |
| DIMENSIONS | LxWxH | 2280.9 x 835.7 x 1181.1 ln (89.8 x 32.9 x 46.5 mm) |
| SOUND LEVEL | | 57 dB(A) |
| VOLTAGE REGULATION | | ± 0.5% |
| 181 MPH WIND RATING | | Optional |

