80/100RE0ZJF

Standby Generators



SKIP THE FORECAST.

KOHLER KEEPS YOU RUNNING IN ANY WEATHER.

When the grid goes down, reliable KOHLER® backup power means the telecom industry keeps running—ensuring communications flow and data remain safe. Designed for cell tower site applications, 80/100REOZJF generators are available in both open and enclosed unit designs.

QUIET PERFORMANCE

Our sound enclosure delivers a sound performance of 69 dBA, which is among the quietest available.

RELIABLE POWER

Our generators meet tough industry testing and quality standards.

SINGLE-SIDE SERVICE

Maintenance is easy. All frequently serviced touchpoints are located on a single side and accessible by an easy-to-remove lift-off door.

MASS CUSTOMIZATION

Kohler makes it easy to customize units for your specific needs and offers options with smaller footprints.

IDEAL PACKAGE SIZE


Our design is competitively sized for cell tower site applications, both open unit and enclosed.

EASY INSTALLATION


We make installation quick and easy with large stub-up areas and easy access to fuel, load and exhaust locations.

80/100RE0ZJF

Front View



Top View



MODEL		80REOZJF & 100REOZJF
FUEL TYPE		Diesel
ENGINE MAKER		John Deere
OPERATING SPEED	(rpm)	1800
CONTROLLER		KOHLER Decision-Maker _® 3000
VOLTAGE		Available in multiple voltages—single-phase & 3-phase
TANK GALLON/48 HRS @ FULL LOAD		448
TANK*		Standard, Double Wall
OVERALL DIMENSIONS (ENCLOSED)	LxWxHin	111 x 45 x 62 Standard Tank
WEIGHT	lb	4,287

^{*}Alternative tank sizes & state tanks available

