

POD SOLUTIONS For Data Centers

MK-PS-DC-PO-EN-221



KOHLER[®]



KOHLER POWER AMERICAS

KOHLER POWER EMEA

KOHLER POWER CHINA

KOHLER POWER INDIA

KOHLER POWER SEA

5 manufacturing locations

15 logistic hubs

10,000+ service providers

THE POWER YOU NEED. ANYTIME, ANYWHERE.

A global force in power solutions since 1920, Kohler is committed to reliable, intelligent products; advanced engineering; and responsive after-sale support.

As the largest privately owned power generation manufacturer in the world, we have 100 years of experience in industrial power and benefit from global R&D, manufacturing, sales, and distribution integration.

KOHLER® PODS POWER OPTIMIZED DESIGNS FOR DATA CENTERS

Inspired by our clients, we developed dedicated solutions for the data center industry worldwide.

Our PODs are designed with standard and reliable components—and available in a variety of configurations. Whether you need to secure the power supply of your data center or simply replace your current backup generators, we have the perfect power options for your business.

Our qualified technical teams will guide you towards the right technical solution for your project, based on your individual requirements and regulations.

KOHLER GUARANTEES LEAD TIMES ON PODS TO PROVIDE **RELIABLE POWER AT A COMPETITIVE VALUE.**

BENEFITS

Short lead time and quick deployment

Optimized design for data centers

Easy for operations

Stackable and rackable solutions

See video
of the PODs



DENSITY PODs

Walk-in enclosure / eFRAME / 45' container
Best power density on the market

HYPERSCALE DATA CENTER

Up to 500 MW



MODULAR PODs

40' container / Skin-tight
Stackable, rackable
Quick deployment

REGIONAL DATA CENTER

Up to 25 MW




X-PRESS PODs

Canopy / Skin-tight / 20' container
Compact
Short lead time

EDGE DATA CENTER

Up to 5 MW





YOUR CHALLENGES OUR EXPERTISE

A data center's electrical power supply can be provided by several different circuits and supplemented by energy storage systems and generators. To provide a “no-break” power supply, data centers need two independent power sources to provide redundancy and risk reduction rather than a single source of inbound power.

Uptime and reliability

Designing power systems that meet the requirement for the highest levels of uptime (e.g. the Uptime Institute Tier IV standard) requires expert attention to system architecture and equipment redundancy. Our priority is to provide you with a reliable and flexible solution for your project, including paralleling two or more generators.

Noise

Our teams focus on generator set design and installation to consider the local environmental impact that noise will have on populated areas and to comply with sound-level regulations all over the world. Kohler measures the sound emitted by all its generator systems, whether open or fully sound-attenuated, to ensure the generator selected is within your site location's noise regulations.

Emissions

Kohler complies with global and local emissions standards (e.g., EPA, MCP, etc.) thanks to our advanced engine design and exhaust equipment. Our KD Series™ generators are specially engineered to allow the lowest levels of emissions particles on the market.

Compact design

The footprint of a generator—in terms of both surface area and volume—is key to ensuring its integration into an environment, regardless of space constraints. That's why KOHLER® generators pack big performance into a compact frame, in both soundproofed and open versions.

YOUR PROJECT OUR PRIORITY

From standard solutions to specific designs, Kohler always supports your needs with a dedicated approach.



1 PLANNING

- Conceptual Design
- Detailed Proposal
- Site Survey & Planning
- Quotation & Recommendation
- Budgeting

2 PROJECT EXECUTION

- Equipment Selection
- Implementation & Construction
- Shop Drawing & Site Preparation
- Equipment Delivery & Installation
- Contracting Agreement & Scope of Work

3 POST-INSTALLATION

- Testing & Commissioning
- Maintenance Contracts
- Functionality Test
- Scheduled Preventive Maintenance
- Training & Documentation
- Emergency Service

Each project submitted to Kohler follows a proven process from planning to the post-installation maintenance. A succession of pre-established steps mastered by all our teams provides you with the guarantee of flawless efficiency.

From planning the design and choice of equipment to final testing and commissioning, we have one goal: to offer you reliable power systems, precisely designed to your specifications. Great flexibility in manufacturing, extreme rigor during testing, meticulous precautions during commissioning—everything is done to provide you with a solution adapted to your activity and your budget.

**GLOBAL STRENGTH
LOCAL SUPPORT**

KOHLER® PODs are predesigned modules, which offer the best solution for scaling your data center power for expansion or incremental growth.

The modules are fully integrated to include a control panel, generating set, monitoring, security, fire system, and cooling.

CHOOSE FROM ONE OF OUR BASE DESIGNS OR CUSTOMIZE FOR YOUR SPECIFIC NEEDS.



Data Center Mission Critical for Continuous Power

Kohler is accredited by the Uptime Institute to deliver DCP rating power for your data center. We are also able to design solutions in compliance with Uptime Institute Tier I to IV requirements.



Standard Features

- Double starter
- Circuit breaker
- Dead bus synchronizing
- Performance class G3
- Class F alternator



Certifications

EMEA

- ISO8528-5
- CE
- EPA Tier 2
- MCP ready

NAFTA

- IBC
- OSHPD/HCAI
- Wind Load
- Missile Impact
- UL2200 Listed
- NFPA 70, 37 & 110
- EPA Tier 2
- EPA Tier 4



Operating Ambient Conditions

- T° min/max: 10°C/50°C
- Humidity: 0%-100%
- Altitude: Up to 1000 m



Options

- IBC compliance
- C4/C5 painting
- SCR treatment
- Fire system
- Double circuit breaker
- Low voltage/medium voltage
- Extreme temperature
- High altitude
- Onboard synchronization capabilities
- Fuel polishing
- Quick-locking devices for mobile external load bank


X-PRESS PODs

Power Optimized Design


EDGE DATA CENTER

Up to 5 MW
Compact and short lead time

50 Hz kWe	500	1440	4000
60 Hz kWe	500	1750	4000



- Enclosure: **Canopy**
- Max Power: **1200 kWe (50 Hz) – 1000 kWe (60 Hz)**
- Sound Level*: 76 dB(A) @ 7 m (SL2, 50 Hz)
82 dB(A) @ 7 m (SL1, 60 Hz)
- Dimensions: L 6.80 x W 2.16 x H 2.75 M
- Fuel System: Belly tank (high fuel capacity for large autonomy)



- Enclosure: **20-ft container**
- Max Power: **1440 kWe (50 Hz) – 1750 kWe (60 Hz)**
- Sound Level*: 72 dB(A) @ 7 m (SL2, 50 Hz)
79 dB(A) @ 7 m (SL2, 60 Hz)
- Dimensions: L 9.14 x W 2.44 x H 2.90 M
- Fuel System: Belly tank (high fuel capacity for large autonomy)



- Enclosure: **Skin-tight**
- Max Power: **1440 kWe (50 Hz) – 1750 kWe (60 Hz)**
- Sound Level*: 79 dB(A) @ 7 m (SL2, 50 Hz)
95 dB(A) @ 7 m (SL1, 60 Hz)
- Dimensions: L 11.15 x W 3.02 x H 4.57 M
- Fuel System: Belly tank (high fuel capacity for large autonomy)

MODULAR PODs

Power Optimized Design

REGIONAL DATA CENTER

Up to 25 MW
Stackable, rackable, and quick deployment

50 Hz kWe	500	1600	2240	4000
60 Hz kWe	500	2000	2500	4000




Enclosure: **Skin-tight**
 Max Power: **2240 kWe (50 Hz) – 2500 kWe (60 Hz)**
 Sound Level*: 78 dB(A) @ 7 m (SL2, 60 Hz)
 90 dB(A) @ 7 m (SL1, 60 Hz)
 Dimensions: L 13.49 x W 3.48 x H 4.78 M
 Fuel System: Belly tank (high fuel capacity for large autonomy)



Enclosure: **40-ft container**
 Max Power: **2240 kWe (50 Hz) – 2500 kWe (60 Hz)**
 Sound Level*: 72 dB(A) @ 7 m (SL2, 50 Hz)
 80 dB(A) @ 7 m (SL1, 60 Hz)
 Dimensions: L 12.19 x W 2.44 x H 2.90 M
 Fuel System: Belly tank (high fuel capacity for large autonomy)

*Typical sound levels. at 50 Hz are at 75% PRP and at 60 Hz are at 100% PRP



DENSITY PODs

Power Optimized Design

HYPERSCALE DATA CENTER

Up to 500 MW
Best power density on the market



Enclosure: **45-ft container**
 Max Power: **2800 kWe (50 Hz) – 3250 kWe (60 Hz)**
 Sound Level*: 80 dB(A) @ 7 m (SL1, 50 Hz)
 74 dB(A) @ 7 m (SL2, 50 Hz)
 Dimensions: L 13.72 x W 2.44 x H 2.90 M
 Fuel System: Belly tank (high fuel capacity for large autonomy)



WALK-IN ENCLOSURES

Enclosure: **Walk-in enclosure + stack SCR ready POD**
 Max Power: **3600 kWe (50 Hz) – 4000 kWe (60 Hz)**
 Sound Level*: 85 dB(A) @ 7 m (SL1, 50 Hz)
 75 dB(A) @ 7 m (SL3, 50 Hz)
 65 dB(A) @ 7 m (SL3, 50 Hz)
 Dimensions: L 17.40 x W 4.01 x H 7.20 M
 Fuel System: Belly tank (high fuel capacity for large autonomy)



Enclosure: **Walk-in enclosure eFRAME™**
 Max Power: **2000 kWe (60 Hz) – 3250 kWe (60 Hz)**
 Sound Level*: 75 dB(A) @ 7 m (SL1, 60 Hz)
 Dimensions: L 15.54 x W 4.19 x H 5.28 M
 Fuel System: Belly tank (high fuel capacity for large autonomy)

*Typical sound levels. at 50 Hz are at 75% PRP and at 60 Hz are at 100% PRP

GUANGZHOU KEYUN DATA CENTER: A POWERFUL CASE STUDY

Generating set: KD2500

Number of gensets: 12

Rackable solution

Frequency: 50 Hz

Engine brand: KOHLER®

Engine model: KD62V12

Voltage: 10.5 kV



Keyun Data Center is located in Guangzhou Economic and Technological Development Zone, with a construction area of 44,091 square meters.


[See video of the Keyun project](#)




Keyun Phase III is the largest data center park built by Guangdong Telecom for Tencent. For this project, Kohler delivered 12 KD2500 gensets with strong project management ability, fast delivery, and after-sale service.

WHERE IN THE WORLD ARE KOHLER DATA CENTER GENERATORS?

With more than 3,000 megawatts (MW) of generator power deployed at data centers globally, and our new 4 MW product leading the way, Kohler is fast becoming the global power partner of choice for data center operators.



AFTERMARKET PARTS AND SERVICE



Global Network

Worldwide distribution locations providing personal customer support and technical assistance 24/7. Consistent world-class parts and service support in all markets we serve.

9 training centers

1,000+ service providers

19 spare parts hubs



Warranty

Kohler stands by the quality of our products by offering a Standard Warranty and optional Extended Warranty to support your investment. All of our equipment is supported by a global network of certified KOHLER distributor technicians and backed by factory-direct technical support services.



Training

Every KOHLER distributor receives technician certification training with Kohler factory instructors in training centers located worldwide. Kohler also hosts training events in Kohler classrooms and labs, as well as on-site training at distributor or customer locations as needed.



Genuine Parts

KOHLER® genuine parts are built specifically for your generator throughout its life cycle and are available when you need them, wherever you are through our global network of distributors.

Preventative maintenance kits are available to provide all the parts required to complete scheduled maintenance events.



Generator Tech Support

As a single point of contact, your Kohler Key Account Service Manager is dedicated to your project.

Our factory-trained and -certified technicians are equipped with the knowledge and latest diagnostic tools to keep your generator up and running with quick, accurate resolutions.

Factory-direct field service engineers support critical installations and field issues as needed.

24/7 service is available nationwide. And hands-on technical support is available from Kohler.



Switchgear Tech Support

Switchgear field service provides 24/7 emergency technical support through our distribution partners.

Qualified technicians are available to respond at a moment's notice and factory support is available when required.

We build lasting relationships, identify potential risks, and mitigate future issues.

Our switchgear support team offers:

- Preventative maintenance
- Risk assessments
- Consistent review of system operations
- Proactive equipment upgrades

North America 800.544.2444

KOHLER®

KOHLERPOWER.COM

PRINTED IN U.S.A. 29270-1 G12-524 3/22 © 2022 BY KOHLER CO.